

Waukesha 15 Positive Displacement Pump

Mfg: Waukesha

Model: 15

Stock No: DBBP185423.9

Serial No: 83154 SS

Waukesha Positive Displacement Pump. Model: 15. Serial No: 83154 SS. Flow rate for new pump is 9 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. (2) 3-1/4 in. rotors. Furnas start/stop switch. Catalog no. 14BP32AC, Series A, 200/230 volts on 1-1/2 phase, 460/575 volts on 2 phase, Max amps 9, 600 VAC, Size 00. Reliance Electric motor drive: 1/2 hp, 9.3 gear ratio, 520 maximum output speeds and 52 minimal output speeds. Reliance Electric motor: hp not specified. 1725 rpm, 230/460 volts, 3.4/1.7 amps, 60 HZ, 3 phase. (1) 1-1/2 in. s-line inlet. (1) 1-1/2 in. s-line outlet. Overall dimensions: 3 ft. 10 in. L x 1 ft. 1/4 in. W x 3 ft. 7 in. H.







