

Philadelphia Mixers Pneumatic Stainless Steel Mixer

Mfg: Philadelphia Mixers

Model: PGA-6-2

Stock No: DBGV325.1a

Serial No: 96AKG1198

Philadelphia Mixers Stainless Steel Pneumatic Mixer. Model: PGA-6-2. S/N: 96AKG1198 This portable, variable speed, clamp on mixer is powered by a pneumatic motor and gear drive which provides maximum torque output, reduces heat build-up and allows for spark free operation. Impeller diameter: 12-1/2 in. Pneumatic motor: 2.0 hp, 1750 rpm. Gear drive ratio: 5:1. Final rpm: 350. Air inlet: (1) 3/8 in. push on air hose fittings. Shaft dimensions: 4 ft. 3-1/2 in. L x 1-1/4 in. diameter. Overall dimensions: 10-5/8 in. L x 1 ft. 1/2 in. W x 5 ft. 6-1/4 in. H. (ACN32)



