

## Bell & Gossett 60 Pump

Mfg: Bell & Gossett

Model: 60

Stock No. DBHK011.

Serial No. 890082

Bell & Gossett 60 Pump. S/N: 890082. Marathon motor,  $\frac{3}{4}$  hp, 1725 rpm, 208-230/460 V, 2.9-3/1.5 FLA, 60 Hz, 3 phase. Pump capacity: 10 gpm at 49.5 ft. head. Flange: 4-3/4 in. with (2) holes, center to center: 3-1/2 in. Inlets/outlets: (2) 1-1/2 in. Overall dimensions: 29 in. L x 10 in. W x 15 in. H.

