

Bell & Gossett Pump

Mfg: Bell & Gossett

Model: 1-1/4AA41

Stock No. DBHK012.

Serial No. 921066/BF

Bell & Gossett Pump. Model: 1-1/4AA41. S/N: 921066/BF. Leeson motor, ¼ hp, 1725 rpm, 115-208/230 V, 4.8-2.4 amps, 60 Hz. Pump capacity: 10 gpm at 15 ft. head. Max. rpm: 1750. Flange: 4-1/2 in. with (2) holes each ½ in., center to center 3 in. Inlet/outlet: (2) 1-1/4 in. Overall dimensions: 17-1/2 in. Lx 13-1/2 in. W x 12 in. H.

