

## Tri Clover PR125 Positive Displacement Pump

Mfg: Tri Clover

Model: PR125

Stock No. DCBJ624.2a

Serial No.           

Tri Clover Positive Displacement Pump. Model: PR125. Maximum capacity @ 20 psi: 120 gpm. Displacement per Revolution: 0.30 gal. Baldor Industrial Motor, 10 hp, 1760 rpm, 208-230/460 V, 28.5-28.4/14.2 amps 60 Hz, 3 phase. Drive, ratio: 4.1, rpm out: 429 (final). Tri-Clover positive displacement pumps handle high viscosity products at elevated GPM and pressure ratings, provide longer seal and rotor life, reduce maintenance costs and downtime, perform effectively on suction lift service, and handle liquids and semi-solids with entrained vapors. Inlets/outlets: (2) 2-1/2 in. dia. S-line fittings. Overall dimensions: 4ft. 1/2 in. L x 1 ft. 6 in. W x 1 ft. 6-1/2 in. H.



