

Evapco PMCA Series Evaporative Condenser- 1170 Tons

Mfg: Evapco

Model: PMCA-1170

Stock No: DFDT02

Serial No: 870072

Evapco PMCA Series Evaporative Condenser. Model: PMCA-1170. Serial No: 870072. Nominal capacity: 1170 tons using R-22 with a 105°F condensing temperature, 40°F suction temperature and a 78°F wet bulb temperature, and 820 tons with R-717 with a 96.3°F condensing temperature, 20°F suction temperature, and a 78°F wet bulb temperature. Mueller pump, model 5G, serial no. 70136-6, 925 gpm, 1750 rpm. (2) pump motor: 7-1/2 hp, 230-460V, 60 Hz, 3 phase. (2) 15 hp fans and (2) 7-1/2 hp fans, 230-460V, 60 Hz, 3 phase. Listed shipping weight: 44,470 lbs. Overall dimensions: 37 ft. 8 in L x 10 ft. W x 13 ft. 2-3/4 in. H.



