

# Krack Low Temperature 4-Fan Blast Evaporator – 57 Tons


Mfg: Krack

Model: POA4H-110-10-3-10-RBA-HGU-RH

Stock No: DFDT13.3a

Serial No: 383357D12

Krack Low Temperature 4-Fan Blast Evaporator. Model: POA4H-110-10-3-10-RBA-HGU-RH. Serial No: 383357D12. Refrigerant: recirculated, bottom-feed R-717 (ammonia). Rated capacity: 650000 BTUH, or 57 tons for a -30°F room with a coil temperature of -40°F. Air at 101000 cfm. (4) 10 hp motors, 1750 rpm, 460V, 60 Hz, 3 phase. This unit has an all-aluminum coil and features hot gas coil and pan defrost. Pipe flow designates this as a “right-handed” unit. Approximate weight 4950 lbs. Overall dimensions: 22 ft. 9 in. L x 4 ft. 2 in. W x 7 ft. 5 in. H.



ADDISON **KRACK** ILLINOIS  
CORP. RH  
POA4H-110-10-3-10-FACTORY  
RBA-HGU-RH  
SERIAL 383357D 12 TYPE REF. R-717  
MOTORS H.P. VOLTS CY. PH. F.L.A.  
4 10 460 60 3 56  
366  
MANUFACTURED 1987