

Cherry-Burrell Votator Scraped Surface Heat Exchanger- 4 x 120



Mfg: Cherry-Burrell





Model: 2C4120LA

Stock No. DFPC282.15

Serial No. 35711VA

Cherry-Burrell Votator Scraped Surface Heat Exchanger- 4 x 120. Model: 2C4120LA. S/N: 35711VA. Jacket MAWP (ammonia side): 100 psi @ 100 °F. Shell MAWP (ammonia side): 200 psi @ 200 °F. Liquid indicator. (18)13-1/2 in. L x 2-3/4 in. W scrapers. Baldor Standard-E Motor, 3 hp, 1750 rpm, 230/460 V, 8.2/4.1 amps, 60 Hz, 3 phase. Inlets: (1) 3/4 in. dia. tube (ammonia), (1) 2 in. dia. S-Line fittings (product), (1) 2 in. dia. copper tube (media). Outlets: (1) 2 in. dia. tube (ammonia), (1) 2 in. dia. copper tube (media), (1) 2 in. dia. S-line fittings (product). Overall dimensions: 11 ft. 3 in. L x 3 ft. 7 in. W x 5 ft.10 in. H.





CAT. NO.		0486111	
SPEC.		3E113TCBBH1	
HP		3	
VOLTS		230/460	
AMPS		6.2/4.1	
R.P.M.		1750	
FRAME		162TC	HZ 60 PH 3
SER. F.		1.15	CODE N DES A CLASS B
NEMA NOM. EFF.		87.5	% PF 78
RATING		400 AMR-CONT	
CC		USABLE AT 200V	
DEARINGS		DE 6203	COE 4225
ENCL.		TEFC	SN F011111111



