

## Rigidbilt Inc. 4-Fan Ammonia Evaporator – 5 Ton

**Mfg: Rigidbilt Inc.**

**Model: UC4-420XA**

**Stock No: DFPC398.1**

**Serial No: 29862**

Rigidbilt Inc. 4-Fan Ammonia Evaporator. Model: UC4-420XA. S/N: 29862. Nominal capacity: 5 tons. Internal volume: 7.69 gal. Nominal fin spacing: 4 fpi. (4) General Electric fan motors, 1/3 hp, 1723 rpm, 230 V, 2.5 amps, 60 Hz, single phase. Fan diameter: 20 in. Inlets: (1) 3/4 in. dia. refrigerant infeed. Outlets: (1) 1 in. suction discharge. Overall dimensions: 10 ft. L x 2 ft. 11 in. W x 2 ft. 9-1/2 in. H.

