

Cherry-Burrell Votator Scraped Surface Heat Exchanger - 6 x 72

Mfg: Cherry-Burrell

Model: 6SSHE

Stock No: DFPC411.21a

Serial No: 89244HA

Cherry-Burrell Votator Scraped Surface Heat Exchanger. Model: 6SSHE. S/N: 89244HA. (1st) votator S/N: A4812. (2nd) votator S/N: A4798. Contact surface area: 9 sq. ft. Shell MAWP: 400 PSI @ 375 °F. Shell MDMT: -20 °F @ 400 PSI. Jacket MAWP: 150 PSI @ 375 °F. Jacket MDMT: -20 °F @ 150 PSI. Motor, 20 hp, 1155 rpm, 405 rpm (final), 230/460 volts, 52/26 amps, 60 Hz, 3 phase. Typical applications are heating and cooling cheese sauce, pudding, caramel, deboned meat, pet food, and fruit products. Pulleys: (1) 7 in. driver, (2) 1 ft. 7 in. driven. Inlets/outlets: (2) 2 in. flanged ports, (2) 1-1/2 in. ACME, (1) 1-1/2 in. MNPT. Overall dimensions: 9 ft. 4-1/2 in. L x 3 ft. 6-5/8 in. W x 4 ft. 6-1/2 in. H.











