

## Alfa Laval Contherm Scraped Surface Heat Exchangers

Mfg: Alfa Laval

Model: 6 x 9

Stock No: DFPC469.67

Serial No: HC2618NCC, HC2688NCC

Alfa Laval Contherm Scraped Surface Heat Exchangers. Model: 6 x 9. S/N: HC2618NCC , HC2688NCC  
Product side MAWP: 300 PSI @ 300 °F. Media side MAWP: 250 PSI @ 300 °F. MDMT: -30 °F @ 100  
PSI. Concentric shafts with (6) 24 in. L x 1-1/2 in. W scrapers. (2) Lincoln A.C. Motors, 7-1/2 hp, 1165  
rpm, 376 rpm (final), 230/460 V, 22/11 amps, 60 Hz, 3 phase. Inlets: (2) 2 in. dia. I-line fittings. Outlet: (2)  
2 in. S-line for ammonia. Overall dimensions: 7 ft. 4 in. L x 5 ft. W x 5 ft. 8 in. H.





