

APV Crepaco R-Series Positive Displacement Pump

Mfg: APV Crepaco

Model: R4RHD

Stock No.: DGPD119.3

Serial No.: R4R-25435

APV Crepaco R-Series Positive Displacement Pump. Model: R4RHD. S/N: R4R-25435. Material of Construction: 316 stainless steel. Nominal Capacity: 160 gpm. Displacement per Revolution: 0.175 gal. Maximum Speed: 900 rpm. APV Crepaco pumps are known for their rugged, long-lasting, and efficient performance. Every pump in the line has standard a stainless steel body, resilient molded rotors, and a heavy duty cast iron gear case which provides long-lasting, economical service over a wide range of products and applications. Its vented cover limits the discharge pressure at a predetermined setting. Reliance Electric Motor, 15 hp, 1760 rpm, 230/460 V, 40/20 amps, 60 Hz, 3 phase. Motor pulley diameter: 7 in. Gear pulley diameter: 8 ½ in. Boston Gear Drive. Inlets/outlets: (2) 3 in. dia. ACME fittings. Overall dimensions: 3 ft. 7 in. L x 3 ft. W x 2 ft. 2 in. H.







