

## York International 6-Cylinder Reciprocating Compressor

Mfg: York

Model: JS64FS-46/50

Stock No. DK102C.

Serial No. KAGR200012

York International 6-Cylinder Reciprocating Compressor. Model: JS64FS-46/50. S/N: KAGR200012. P/N: 554-83012. Refrigerant: R-22. Power supply: 460-380/415 V, 759/575-761/570 amps, 60/50 Hz, 3 phase. Inlets: (1) 2-1/2 in. dia. copper refrigerant port. Outlets: (1) 3 in. dia. copper refrigerant discharge port. Overall dimensions: 4 ft. 11 in. L x 3 ft. 4 in. W x 3 ft. 4 in. H.





