

2004 Niro Inc. Vacuum Chamber Skid

Mfg: Niro Inc.

Model:

Stock No. DLEC047.22

Serial No. JS2588

2004 Niro Inc. Vacuum Chamber Skid. National Bø No. 5569. S/N: JS2588. Equipment No. VLS-9532. Drawing No. JS-2588. ESP Control Panel. Project No. 3544. S/N: 0947. Drawing No. 03312132-13G1-532. Power supply: 120 V, 60 Hz, single phase. Overall dimensions: 7 ft. L x 3 ft. 8 in. W x 7 ft. 7 in. H.

DCI Vacuum Chamber. 316 Stainless Steel construction. Vessel MAWP: 45/-15 psi @ 350 °F. MDMT: -20°F @ 45 psi. Volume: 50 gallons. Top head & BTM thickness: .1875 in. /.165 in. Shell thickness: .135 in. Inlets: (5) 1-1/2 in. dia. S-line fittings. Outlets: (1) 2-1/2 in. dia. S-line fittings.

(5) GEA Flow Diversion Valves. Inlets/outlets: (2) 2 in. dia. S-line fittings.

Busch Mink Vacuum Pump. Model: MM1144 AV. S/N: 04004055. Nominal suction capacity: 96 m3/h. Baldor Industrial Motor, 3 hp, 1760 rpm, 460 V, 4 amps, 60 Hz, 3 phase. Inlets: (1) 2 in. dia. NPT fittings. Outlets: (1) 1-1/2 in. dia. NPT fittings.

Fristam Sanitary Centrifugal Pump. Model: FZX2100. S/N: FZX21000400169. Baldor Industrial Motor, 3 hp, 1760 rpm, 460 V, 4 amps, 60 Hz, 3 phase.











