

Indeeco Electric Duct Heater

Mfg: Indeeco

Model: TFZU

Stock No.: DLEC076.a

Serial No.: 4D04 79185

2004 Indeeco Electric Duct Heater. Type: TFZU. 20.6 KW. DWG No. L931N1: c19159-A-0. P.O. No. RJ04-380. Tag No. RHC-9402.2. Control Panel. Catalog No. 103-A3-480-20I. S/N: 4D04 79186. Panel power supply: 480 V, 30 amps, 3 phase. (6) Tubular finned coils. No. of steps: 1. Coil dimensions: 1 in. dia. x 3 ft. L. Heater power supply: 25 hp, 480 V, 60 Hz, 3 phase. Inlets/outlets: 3 ft. L x 1 ft. W (duct). Indeeco duct heaters utilize the finest of construction principle and techniques. The coil is constructed of a .475 in diameter stainless steel sheath and contains a 80% nickel, 20% chromium resistance wire insulated from the sheath by a magnesium oxide powder, compacted to rock-like density. The elements are flanged, making them individually removable. All heaters are suitable for installation in ducts with up to one inch of interior lining. Overall dimensions: 6 ft. L x 1 ft. 5 in. W x 3 ft. 4 in. H. (ACN31a).



