

Indeeco Electric Duct Heater

Mfg: Indeeco

Model: TFZU

Stock No.: DLEC088.1a

Serial No.: 1E04 79515

Indeeco Electric Duct Heater. Type: TFZU. DWG No. L931N1: C19159-A-0. P.O. No. RJ04-380. Tag No. RHC-9401.6. Control Panel. Catalog No. 103-A3-480-20I. S/N: 1E04 79515. 1.7 KW. Panel power supply: 480 V, 20 amps, 3 phase. (2) Tubular finned coils. No. of steps: 1. Coil dimensions: 1 in. dia. x 8 in. L. Heater power supply: 2 hp, 480 V, 60 Hz, 3 phase. This is a flanged unit. Inlets/outlets: 10 in. L x 6 in. W (duct). Indeeco duct heaters utilize the finest of construction principle and techniques. The coil is constructed of a .475 in diameter stainless steel sheath and contains a 80% nickel, 20% chromium resistance wire insulated from the sheath by a magnesium oxide powder, compacted to rock-like density. The elements are flanged, making them individually removable. All heaters are suitable for installation in ducts with up to one inch of interior lining. Overall dimensions: 1 ft. 10 in. L x 11 in. W x 5 ft. H. (ACN6).



PROPERTY TAG
DO NOT REMOVE

Slip

D03937

ELECTRIC DUCT HEATER

INDEECO

ST. LOUIS, MISSOURI

INDEECO CATALOG NUMBER

1F2U 1.7 10x5 ES4C

CODE TYPE KW DIMENSIONS MFG. DATE

480 03 01 024

VOLT PHASE NO. OF CONTROL STEPS VOLTS CONTROL CIRCUIT POWER

BACACBES34E22HTH3L5M3P2P3P4003T1U5Z2Z

SPECIAL FEATURE CODE

SUPPLY INFORMATION IN ABOVE BOX WHEN CONTACTING FACTORY

CUSTOMER FURNISHED INFORMATION

RJ04-380 RHC-8401.6

P.O. NUMBER ITEM TAG NUMBER

MODEL NUMBER

ST. LOUIS, MISSOURI

INDEECO CATALOG NUMBER

1F2U 1.7 10x5 ES4C

CODE TYPE KW DIMENSIONS MFG. DATE

480 03 01 024

VOLT PHASE NO. OF CONTROL STEPS VOLTS CONTROL CIRCUIT POWER

BACACBES34E22HTH3L5M3P2P3P4003T1U5Z2Z

SPECIAL FEATURE CODE

SUPPLY INFORMATION IN ABOVE BOX WHEN CONTACTING FACTORY

CUSTOMER FURNISHED INFORMATION

RJ04-380 RHC-8401.6

P.O. NUMBER ITEM TAG NUMBER

MODEL NUMBER

MOUNT WITH ARROW UP

AIRFLOW DIRECTION

↑

↓

