

## Transfer Inclined Cleated Conveyor

Mfg:

Model:

Stock No. DPF1209.1a

Serial No.

Transfer Inclined Cleated Conveyor. Stainless steel construction. Maximum aperture/clearance above belt: 16 in. W x 6-1/2 in. H. Sew Eurodrive Motor, 1 hp, 1,700 rpm, 230/460 V, 3.70/1.85 amps, 60 H z, 3 phase. Sew Eurodrive, 19.13 ratio, 89 rpm (final), 585 lb-in torque. Overall dimensions: 12 ft. L x 30-1/2 in. W x 8 ft. H.

