

1999 Sabroe Reciprocating Compressor-125 HP

Mfg: Sabroe

Model: SMC106 E

Stock No. DPF1430.4

Serial No.

1999 Sabroe Reciprocating Compressor- 125 HP. Model: SMC106 E. Shop No: 111541. Cylinders: 6. Refrigerant: R-717. Max speed: 1500 rpm. Swept volume: 300 cfm. Max crankcase pressure: 319 psig. MAWP: 609 psig. Baldor Super-E Motor, 125 hp, 1785 rpm, 460 V, 140 amps, 60 Hz, 3 phase. Inlets: (1) 3 in. dia. pipe. Outlets: (1) 2 in. dia. pipe. Overall dimensions: 96 in. L x 50 in. W x 53 in. H. M&M Refrigeration Control Panel with touchpad controls and digital display. 1999 M&M Refrigeration Holding Tank, S/N: 99B012, MAWP @ 650 °F: 300 psig. MDMT @ 300 psig: -20 °F. (2) Henry Valve Company Pressure Relief Valves, Cat. No: 5604, set psi: 300, capacity: 59.4 lbs air/min. Starter included.





