

Vilter Reciprocating Compressor, Size 448

Mfg: Vilter

Model: 448

Stock No. DPFI432.2

Serial No. 13724A RC

Vilter Reciprocating Compressor. Size 448. S/N 13724A RC. Order No. C740151. Refrigerant: Ammonia. Displacement at maximum rpm: 309 cu. ft./min. Number of cylinders: 8. Electrical requirements: 110 V. Lincoln Motor, 100 hp, 1761 rpm, 230/460 V, 232/116 amps, 60 Hz, 3 phase. Inlets: (1) 4 in. dia. pipe. Outlets: (1) 3 in. dia. pipe. Penn Oil Failure Cut In/Out controls. Overall dimensions: 78 in. L x 48 in. W x 68 in. H.

