

Cross Over Conveyor

Mfg:	Model:
Stock No. DSBI128.2a	Serial No.

Cross Over Conveyor. Maximum aperture/clearance above belt: 12 in. W x 5 in. H. Height at conveyor inlet/outlet: 34 in. Conveyor features a 9 ft. L x 14-1/2 in. W x 5 in. H hinged, bottom-mounted collecting trough. Baldor Industrial Motor, 1/2 hp, 1725 rpm, 208-230/460 V, 1.8-1.6/0.8 amps, 60 Hz, 3 phase. Dayton Motor Drive, 60:1 ratio, 28.75 rpm (final). Outlets: (1) 14 in. W x 5 in. H discharge chute. Overall dimensions: 12 ft. 3 in. L x 32 in. W x 40 in. H.

