

## Tri Clover PR25 Positive Displacement Pump

Mfg: Tri Clover

Model: PR25-1-1/2-VC4ST-S

Stock No. DSLP036.16

Serial No. T3827J

Tri Clover PR25 Positive Displacement Pump. Model: PR25-1-1/2-VC4ST-S. S/N: T3827J. U.S. Motor, 1 hp, 1725 rpm, 200-230/460 V, 5.5-4.8/2.4 amps, 60 Hz, 3 phase. Vari-Drive Module, ratio: 20.6, min/max speed: 21/208 rpm. Inlets/outlets: (2) 1-1/2 in. dia. ACME fittings. Overall dimensions: 30 in. L x 18 in. W x 18-1/2 in. H.





