

Micro Motion Mass Flow Meter System

Mfg: Micro Motion

Model: L065S242

Stock No. DSLP189.3a

Serial No. 151544

Micro Motion Mass Flow Meter System. Model: L065S242. S/N: 151544. Tube: 1500 psig. Connection type: clamp. Temp: -240 to 177 °C. Sensor: DL665S242. S/N: 151544. Meter type: 34. Meter factor: 19829. Flow calibration factor: 19.8295.13. Density calibration factor: 11287133404.44. Inlets/outlets: (2) 1 in. dia. S-line fittings. Overall dimensions: 24-1/2 in. L x 14-1/2 in. W x 10-1/2 in. H.



MODEL: L065S242
S/N: 151544
TUBE: 1500 PSIG

TELEMETERING EQUIPMENT FOR
LY SAFE FOR CLASS 1, GR. C AND
DIV. 1, AND ALSO SUITABLE FOR C

Dens Cal Factor 11237133404,
Cal Factors Ref to 0°C

TEMP -240 TO 177
TUBE: 1500 PSIG

**MAX. PRESSURE RATING AT 25°C ACCORDING TO S
**MAX. PRESSURE RATING AT 25°C ACCORDING TO S

MME
28

151544

Sensor L065S242 S/N
Meter Type 30
Meter Factor 19823
Flow Cal Factor 19.8295, 13
Dens Cal Factor 11237133404, 40
Cal Factors Ref to 0°C

TEMP -240 TO 177 °C
TUBE: 1500 PSIG