

## Ingersoll-Dresser Centrifugal Pump - 4x3x10

**Mfg: Ingersoll Dresser**

**Model:**

**Stock No: DTTC2049**

**Serial No: 0201-7931/A H0C3+**

Ingersoll-Dresser Centrifugal Pump. S/N: 0201-7931/A H0C3+. Size: 4x3x10. Ref. No: A273077. Impeller diameter: 10.75. Maximum impeller size: 10.75. Maximum design pressure: 275 psig. Baldor Industrial Motor, 15 hp, 1765 rpm, 230/460 V, 37/18.5 amps, 60 Hz, 3 phase. Inlets: (1) 4 in. dia. flanged port. Outlet: (1) 3 in. dia. flanged port. Overall dimensions: 4 ft. 10 in. L x 2 ft. W x 2 ft. H.





