

1993 FES 775 / Mycom 320 SU-MX Rotary Screw Compressor Package – 1000 HP

Mfg: FES / Mycom

Model: 775 / 320 SU-MX

Stock No: DTTC2067

Serial No: 3251465

1993 FES 775 / Mycom 320 SU-MX Rotary Screw Compressor Package. Model: 775 / 320 SU-MX. S/N: 3251465. FES contract no: 93147032. Refrigerant R-717. Mycom rotary screw compressor, Model: 320 SU-MX. S/N: 3251465. Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. Nominal capacity: 825 tons at 936.2 bhp with a 95°F condensing temperature and a 20°F suction temperature. Vi setting: 3.6. Displacement: 2,230 cfm. 1993 FES oil separator, S/N: 930197, Nat'l Bd: 6425, MAWP: 250 psi @ 200°F, MDMT: -20°F @ 250 psi. Westinghouse World Series electric motor, 1000 Hp, 3580 rpm, 4160V, 122 amps, 60 Hz, 3 phase. FES Micro II E control panel. Viking rotary positive displacement pump, P/N: 3-551-002-340-EN. Reliance electric motor, 10 Hp, 1755 rpm, 230/460 V, 27/13.5 amps, 60 Hz, 3 phase. Inlet: (1) 10 in. dia. refrigerant suction port. Outlet: (1) 6 in. dia. refrigerant discharge port. Compressor run time: 6,429 hrs. since Mycom rebuild. Overall dimensions: 16 ft. 1 in. L x 5 ft. 2 in. W x 9 ft. 10 in. H. CF (ACN1450)











