

Fisher Pneumatic Valve Positioner

Mfg: Fisher

Model:

Stock No.: DTTC2093

Serial No.: 14526908

Fisher Pneumatic Valve Positioner. S/N: 14526908. Type: 1051. Size: 60. Range: 0-18 psi. Rotation: 90°. Fisher Body, type: V300, size: 10, rating: CL300, body: STL, shaft: SST, seat: COMP, ball/disc: SST/PL. Inlet: (1) 10 in. dia. ANSI flange class 300. Outlet: (1) 10 in. dia. ANSI flange class 300. Overall dimensions: 2 ft. 9 in. L x 1 ft. 8 in. W x 3 ft. 4 in. H. (ACN121a).



FISHER BODY		Fisher Controls	
SERIAL NO.	14526908	TYPE	1051
SIZE	60		
RATING	CL300		
BODY	STL	BALL/DISK	SST/PL
SHAFT	SST	SEAT	COMP
FOR FLANGE SIZE AND MAX TEMP SEE PRODUCT LITERATURE			
ACTUATOR		Fisher Controls	
MODEL NO.	14526910	TYPE	1051
PRESS. UNITS	PSI	SIZE	50
INSTR. SET	N/A	OPER. RANGE	0-18
ASSEMB.	1051	ROTATION	90 DEG

