

FES 385-ME / Mycom 250S Screw Compressor Package - 450 HP

Mfg: FES Mycom

Model: 385-ME/250S

Stock No.: DTTC829

Serial No.: 2552297

FES 385-ME / Mycom 250S Screw Compressor Package - 450 HP. Model: 385-ME/250S. S/N: 2552297. Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. Displacement: 1,110 cfm. Oil separator, Nat'l Bd: 1075. MAWP: 250 psi. Maximum temperature: 300 °F. Toshiba motor, 450 hp, 3540 rpm, 2300/4160 V, 100/55 amps, 60 Hz, 3 phase. Viking rotary pump, Model: AL 4195, S/N: 11676904. Toshiba motor, 7-1/2 hp, 1170 rpm, 230/460 V, 22.2/11.1 amps, 60 Hz, 3 phase. Mycom Mypro-M control panel. Inlets: (1) 16 in. dia. ammonia flange, (1) 1 in. dia. ammonia port, Outlets: (1) 5 in. dia. ammonia port. Overall dimensions: 13 ft. 3 in. L x 4 ft. 5-1/2 in. W x 8 ft. 2 in. H. (SR250) (ACN845). CF









