

Perma San Dimple Jacketed Vertical Tank-1400 Gallon

Mfg: Perma San

Model: 1400 gallon JCVC

Stock No. DTWA398.40

Serial No. 43702-1

Perma San Side and Bottom Dimple Jacketed Vertical Tank-1400 Gallon. Model: 1400 gallon JCVC. S/N: 43702-1. National Board: 4899. 304 Stainless steel construction. Jacket: 50 psi at 300 °F. Shell: 0.103, head thickness: 0.110. Crown radius: 84 in. Siemens Allis agitator motor: 5 hp, 1745 rpm, 230/460 V, 13.44/6.72 amps, 60 Hz, 3 phase. Eurodrive gear motor, input max: 1750 rpm, final rpm: 43, torque: 5790 Lb-in. Flange-mounted agitator, shaft: 150 in. L x 2-1/2 in. diameter, (3) propellers: 36 in. L. (2) Spray ball system, manway: 18 in. diameter, temperature gauge. Product inlet: 3 in. threaded (female), spray ball inlet: 2 in. treaded (male), jacket inlet: 1 in. threaded (female) outlet: 2 in. threaded (male). Overall dimensions: 66 in. diameter x 15 ft. H.



