

## Will Flow Stainless Steel Jacketed Tank with Lightnin Mixer – 2000 Gallons

Mfg: Will Flow

Model:

Stock No. DTWA403.51

Serial No. 11409

Will Flow Stainless Steel Jacketed Tank with Lightnin Mixer- 2000 Gallon. S/N: 11409. Nat'l Bd: 788. 316 SS. Inside straight-wall dimensions: 78-1/2 in. dia. x 113 in. H. Jacket MAWP: 125 psi at 360 °F. Shell thickness: 0.172 in. Head thickness: 0.172 in. Crown radius: 89 in. (4) 96 in. L x 6 in. W internal baffles. Lightnin Heavy Duty Agitator Drive, Model: 314-TELB-30.2, S/N: 684417, shaft diameter: 3 in., flange diameter: 7-1/2 in. Louis-Allis Pacemaker Motor, 30 hp, 1780 rpm, 155 rpm (final), 460 V, 37.5 amps, 60 Hz, 3 phase, 11.41 ratio. Stainless Steel Agitator, impeller type: A200, number of impellers: 2, impeller diameter: 2 ft. 7 in., blade width: 6 in., shaft diameter: 3 in., shaft length: 9 ft. 4 in. Inlets: (2) 25 in. W x 71 in. L (top infeed), (2) 2 in. dia. FNPT fittings (media), (1) 1 in. dia FNPT fitting. Outlets: (1) 2-1/2 in. dia. ACME fitting (product out), (2) 2 in. dia. FNPT fitting (media).







