

Waukesha 30 Positive Displacement Pump

Mfg: Waukesha

Model: 30

Stock No.: DWKN213.15

Serial No.: 82613SS

Waukesha 30 Positive Displacement Pump. Model: 30. S/N: 82613SS. Flow rate for new pump is 30 gpm with required horsepower. Current capacity with drive: 25 gpm. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Features include: easy cleaning and disassembly, three-way mounting options, and non-galling Waukesha "88" alloy rotors. Maximum pressure: 200 psi. Maximum speed: 600 rpm. Temperature range: -40°F to 300°F. 316 Stainless steel pump body, cover and shaft. 2hp SEW Eurodrive in-line gear motor, 3.95-1 ratio, 435rpm output at pump, 230/460V, 3-ph, 60hz, with manual starter. 1-1/2" tri-clamp inlet & outlet. Unit is mounted on a 1 ft. x 2 ft. 6 in. stainless steel base plate with casters.(ACN72).





