

Waukesha 60 Positive Displacement Pump

Mfg: Waukesha

Model: 60

Stock No.: DWKN216

Serial No.: 143181

Waukesha 60 Positive Displacement Pump. Model: 60. S/N: 143181. Flow rate for new pump is 80 gpm with required horsepower. Current capacity with drive: 12 gpm. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Features include: easy cleaning and disassembly, three-way mounting options, and non-galling, Waukesha "88" alloy rotors. Maximum pressure: 200 psi. Maximum speed: 600 rpm. Temperature range: -40°F to 300°F. 316 stainless steel pump body, cover and shaft. Seal option: single mechanical. Sew-Eurodrive motor, 2 hp, 1720 rpm, 230/460 V, 6.0/3.0 amps, 60 Hz, 3 phase. Sew-Eurodrive speed reducer, ratio: 20.91, rpm out: 82 (final). Inlets/outlets: (2) 2-1/2 in. dia. ACME fittings. Overall dimensions: 3 ft. 8 in. L x 1 ft. 4 in. W x 1 ft. 8 in. H.(ACN110).





