

Vilter VRS-900B / WRV204/1.65 Howden Rotary Screw Compressor Package - 125 HP

Mfg: Vilter / Howden

Model: VRS-900B / WRV204 /1.65

Stock No: DWKN4002

Serial No: MK4B/WRV204/16526/1114

Vilter VRS-900B / WRV204/1.65 Howden Rotary Screw Compressor Package. Model: VRS-900B/WRV204/1.65. S/N: MK4B/WRV204/16526/1114. Contract No: JH1109. Vilter order no. E-35188-2. Capacity rating: 308 tons at 357 BHP using R-717(ammonia) with suction temperature of 20°F / 33.5 psig and condensing temperature of 95°F and 181 psig. Displacement: 853 cfm. Baldor Electric Co. Motor: Cat. No. EM2554T-4. 125 HP, 3570 rpm, 404TS, ser. no. P5-95, 460v, 60 Hz, 3 phase. Estimated shipping weight: 7100 lbs. Total hours on compressor: 24,194. Overall dimensions: 13 ft. 7 in. L x 4 ft. 4 in. W x 8 ft. 4 in. H.









