

## FMC Dual Piston Filler

Mfg: FMC

Model:

Stock No. EEGC115.2a

Serial No.

FMC Dual Piston Filler. Traveling head (maximizes time in the product zone). Pneumatic. Valve dia.: 1-1/2 in. Center between valves/heads: 7-1/8 in. Maximum filler volume: 1/2 liter (16.9 oz.). BPM: 20. Tank volume: 180 liters (approx. 47.5 gal). SEW Motor, 1/2 hp, 1750 rpm, 220 V. SEW Motor Drive, ratio-14.31, rpm-460 in/32 out, torque 130. Overall dimensions: 70 in. L x 50 in. W x 62 in. H.



