

## Ammonia Vertical Intercooler- 32 in. Dia. 8 ft. 2 in. H

Mfg:

Model:

Stock No: EELD664A.1a

Serial No:

Ammonia Vertical Intercooler- 340 Gallon. Inside straight-wall dimensions: 2 ft. 8 in. dia. x 8 ft. 2 in. H. Parker Float Switch, Type: LL, refrigerants: NH<sub>3</sub>, R-12, R-22, R-502, maximum temperature: 150°F, power supply: 120/240 V, 10 amps. Inlets: (2) 1 in. dia. liquid feed ports, (1) 6 in. dia. booster inlet port. Outlets: (1) 1/2 in. dia. FNPT (pressure relief), (1) 3/4 in. dia. oil pot drain, (1) 1 in. dia. drain port, (1) 6 in. dia. gas outlet port. Overall dimensions: 5 ft. 1 in. L x 3 ft. 4 in. W x 12 ft. H.



