

Tri-Clover Positive Displacement Pump

Mfg: Tri-Clover

Model: PR60-3-TC1-4-ST-S

Stock No: EFMA02

Serial No: W7587

Tri-Clover Positive Displacement Pump. Model: PR60-2-TC1-4-ST-S. S/N: W7587. Flow rate for new pump is 60 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Reliance Electric motor: 7.5 hp, 1760 rpm, 230/460 v, 18.0/9.0 a, 60 hz, 3 phase. Motor drive: 5.0 ratio, 1750 input rpm, 350 output rpm, 3495 torque. (2) 5-3/4 in. rotors. Inlet/outlet: (2) 2 in. ACME. Overall dimensions: 4 ft. 2 in. L. x 1 ft. 10 in. W. x 2 ft. H.





