

Sullair Ammonia Booster Compressor

Mfg: Sullair

Model: B25LB717-2.8

Stock No: EKTF9311.9

Serial No: 056-01628

Sullair Ammonia Booster Compressor. Model: B25LB717-2.8. S/N: 056-01628. WD/N: 067129. Compressor run time 43887. MAWP: 150 psig. Reliance Electric Motor, 200 hp, 3,550 rpm, 460 V, 231 amps, 60 Hz, 3 phase. Inlets: (1) 8 in. dia. suction pipe with a 12-3/4 dia. flange and (12) 3/4 in. holes at a center-to-center distance of 11-3/4. Outlets: (1) 6 in. dia. discharge pipe with a 12-1/2 in. flange and (12) 3/4 in. holes at a center-to-center distance of 10-1/2 in. Tuthill Motor with Oil Pump, 1/4 hp, 1,725 rpm, 115/230 V, 11/0/5.5 amps, 60 Hz, single phase. Overall dimensions: 11 ft. 7 in. L x 4 ft. 6 in. W x 6 ft. H.



