

## Bell and Gossett Centrifugal Pump

**Mfg: Bell and Gossett**

**Model: 6BC9.125BFH00**

**Stock No. EKTF9384.2a**

**Serial No. 2229253**

Bell and Gossett Centrifugal Pump. Model: 6BC9.125BFH00. S/N: 2229253. Capacity: 1200 gpm. Impeller dia. 9.125. TDH: 72 ft. MAWP: 175 psi. U.S. Motor, 30 hp, 1,765/1,445 rpm, 208-230/460 V, 80.0-72.0/36.0 & 90.0/45.0 amps, 60/50 Hz, 3 phase. Inlets: (1) 8 in. dia. suction with a 14-3/4 in. dia. flange and (8) 3/4 in. dia. attachment holes at a center-to-center distance of 12 in. Outlets: (1) 6 in. dia. discharge valve with an 11 in. dia. flange (8) 3/4 in. dia. attachment holes at a center-to-center distance of 9-1/2 in. Overall dimensions: 55 in. L x 22 in. W x 45 in. H.

Bell & Gossett Triple Duty Valve, Model: 3PS-6S, MAWP: 175, max. temperature: 250 °F.

