

Wright Series TRA10 Positive Displacement Pump

Mfg: Wright Pump

Model: 0150

Stock No: EMRW004

Serial No: 07G4967

Wright Series TRA10 Positive Displacement Pump. Model: 0150. S/N: 07G4967. Flow rate for new pump is 9 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Maximum pressure: 200 psi. Leeson Electric motor: 1 hp, 1725 rpm, 115/208-230 v, 12.8/6.4 a, 60 Hz, 1 phase. Motovario Corp drive. Model: HA42, S/N: 46012, ratio: 8.11. (2) 3-1/4 in. stainless steel rotors. (1) Emergency stop button. Wright Pump's TRA10 series circumferential piston pumps are drop-in replacements for Waukesha® U1 and U2 series pumps. Wright TRA10 series are the traditional workhorse pumps designed for strip-clean (C-O-P) applications. Inlet/outlet: (2) 1-1/2 in. ACME. Overall dimensions: 3 ft. 7-1/2 in. L x 1 ft. 4 in. W x 3 ft. 3-1/4 in. H.









