

Norwalt Design Cap Feeder

Mfg: Norwalt Design

Model:

Stock No. ENAE001.

Serial No. F-1622-1

Norwalt Design Cap Feeder. S/N: F-1622-1. Job: N-1622. Sorts: 1-1/2 in. L x 1-1/2 in. W deodorant caps. Disc diameter: 36 in. Cincinnati Fan and Ventilator Co. Blower, Model: PB-10A, S/N: 9300245. Reliance Electric Motor, 3/4 hp, 3450 rpm, 208-230/460 V, 2.4-2.4/1.2 amps, 60 Hz, 3 phase. Gast RegenAir Blower with Reliance Electric Motor, Model: R3305A-1, S/N: 0294, cfm: 53/44, max. pressure/vacuum: 43 in. H₂O/31 in. H₂O-40 in. H₂O/28 in. H₂O, 60/50 Hz. Reliance Electric Drive Motor, 1/4 hp, 1750 rpm, 90 V, 2.70 amps. Grove Gear Flexaline, 10 ratio, 175 rpm (final). Inlets: (1) 12 in. L x 10 in. W infeed. Outlets: (1) 4 in. L x 3 in. W discharge chute. Overall dimensions: 5 ft. 10 in. L x 3 ft. 6 in. W x 7 ft. 2 in. H.



