

## Horizontal Jacketed Holding Tank 6,000 Gallons

<b>Mfg:</b>	<b>Model:</b>
<b>Stock No. END58401.58</b>	<b>Serial No. 78934</b>

Horizontal Jacketed Holding Tank- 6,000 Gallon. S/N 78934. (3) spray balls on top, (2) double agitators. Atlas tank pump: type 407059, S/N Y5A54. Inlet/outlet: (2) 4 in. Lincoln Electric Motor: 10 hp, 1,745 rpm, 575 V, 60 Hz, 10.4 amps, 3 phase. Inlet/outlet descriptions: 20 in. manway, 1-1/2 in. jacketed input/output, 1/2 in. input/output, 2 in. bottom drain, 1-1/2 in. input/output bottom, 1-1/2 in. input/output bottom, 1/2 in. temp. input, 3/4 in. temp. input, 4 in. top window. Outside dimensions: 18 ft 9 in. L x 8 ft 7 in. W x 10 ft 7 in. H.



