

Groen Kettle-50 Gallon

Mfg: Groen

Model: Model TA-40

Stock No. END81586.14a

Serial No.

1979 Groen Kettle-50 Gallon.

- Model TA-40
- National Board No. 97807,
- Max Working pressure 125 psi at 353 °F.
- Type 316 SS.
- Motor: 1 hp, 1,725 rpm, 460 volt, 2.3 amps, 60 hz, 3 phase, FB56C.
- Drive Reeves Vari Drive, Reliance. Size 100, 1 hp, Output rpm: 538 (min), 2,150 (max).
- Inside dimensions: 28 in. diameter, 22 in. H. (At center).
- Has 2 agitators (same drive), and a fixed baffle.
- Inlets (1) 1 in.
- 2 removable lids.
- Outlets: (1) 3 in. with valve.
- Overall dimensions: 29-½ in. W, 36 in. L, 84-½ in. H.



