

Mycom 4-Cylinder Reciprocating Compressor – 25 HP

Mfg: Mycom

Model: N4A

Stock No.: ENDX716.4

Serial No.: 10452

Mycom 4-Cylinder Reciprocating Compressor. Model: N4A. S/N: 10452. Refrigerant: ammonia. Leak test pressure (hi/lo): 313/157 psig. Hydrostatic test pressure (hi/lo): 470/470 psig. Shell and tube oil cooler. Liquid-cooled heads. WEG Motor, 25 hp, 1770 rpm, 575 V, 23 amps, 60 Hz, 3 phase. Drive pulley diameter: 8 in. Gear pulley diameter: 16 in. Inlets: (1) 3/4 in. dia. port (liquid), (1) 2 in. dia. globe valve (refrigerant suction). Outlets: (1) 3/4 in. dia. port (liquid), (1) 2 in. dia. globe valve (refrigerant discharge). Overall dimensions: 6 ft. 5 in. L x 3 ft. W x 4 ft. 8 in. H.





