

Mycom Ammonia Compressor Model C5WO4A

Mfg: Mycom

Model: C5WO4A

Stock No. ENDX718.3a

Serial No. 95690

Mycom Ammonia Compressor. Model C5-WO4A, S/N 95690. Inlets/outlets 2 in. 2-1/4 in. Minimum Test Pressure:(PSIG) HYD: High pressure: 450, Low pressure: 300. AIR: High pressure: 300, Low pressure: 180. U.S. Electrical Motor, 25 hp, 1,775 rpm, 575 V, 24 amps, 60 Hz, 3 phase. Overall Dimensions 81 in. L x 38 in. W x 50 in. H.

