

APV Crepaco R-Series Positive Displacement Pump

Mfg: APV Crepaco

Model: R3RX

Stock No: ENDX751.1a

Serial No: D-1363

APV Crepaco R-series Positive Displacement Pump. Model: R3RX. S/N: D-1363. Capacity: 23 gpm. Displacement per Revolution: 0.064 gal. Material of construction: 316 Stainless Steel.. Maximum speed: 900 rpm. Reliance Electric Motor, 2 hp, 1725 rpm, 359 rpm (final), 230/460 V, 5.4/2.7 amps, 60 Hz, 3 phase. APV Crepaco R-series pumps are known for their rugged, long-lasting, efficient performance. Every pump in the line has as standard a stainless steel body, resilient molded rotors, and a heavy cast iron gear case, which provides long-lasting, economical service over a wide range of products and applications, easy disassembly and cleanup, low maintenance. Typical applications include: fruit cocktail, yogurt, alcoholic beverages, dough, chocolate and shampoo. Inlets/outlets: (2) 1 ½ in. dia. ACME fittings. Overall dimensions: 3 ft. 3 ½ in. L x 1ft. 3 ½ in. W x 1ft. 10 in. H.



