

APV R6R Positive Displacement Pump

Mfg: APV

Model: R6R

Stock No. ERCS001B.

Serial No. H-3162

APV R6R Positive Displacement Pump. Model: R6R. S/N: H-3162. Pumping capacity: 15 gpm @ 82 rpm. Maximum capacity: 150 gpm. Maximum speed: 900 rpm. Displacement per 100 revolutions: 29 gpm. Baldor Industrial Motor, 5 hp, 1725 rpm, 208-230/460 V, 15-13.2/6.6 amps, 60 Hz, 3 phase. Reeves Varidrive Module, 31.4 ratio, 28/84 rpm (min/max) Complete parts interchangeability. Easy disassembly and cleanup, low maintenance. Typical applications: fruit cocktail, yogurt, alcoholic beverages, dough, chocolate and shampoo. Inlets/outlets: (2) 3 in. dia. S-Line fittings. Overall dimensions: 47 in. L x 17 in. W x 31 in. H.



