

## Saftronics G3+ Adjustable Frequency AC Drive Control Panel

Mfg: Saftronics

Model: CIMR-G3U4037+

Stock No. ERCS054.

Serial No. 138909

Saftronics G3+ Adjustable Frequency AC Drive Control Panel. Model: CIMR-G3U4037+. S/N: 138909. AC Input: 380-460 V, 99.0 amps, 50/60 Hz, 3 phase, 68.0 KVA. A.C. Output: 0-460 V, 0-400 Hz, 3 phase. Acme Transformer. Overall dimensions: 37-1/2 in. L x 14 in. W x 72 in. H.



