

North Star Pneumatic Ice Delivery Blower

Mfg: North Star Ice

Model:

Stock No.: EZPR07

Serial No.:

North Star Flake Ice Blower for ice delivery. Pneumatic ice delivery is one of the best options for moving ice over long distances (up to 400-800 feet depending on the application). Features a Gardner Denver DuroFlow Industrial 45 Series Blower. Model: GGDDADA. Serial: S305676. Catalog 4512. Max RPM: 400. Leeson motor: 75 HP, 208-230/460V, 188-172/86 amps, 3560 RPM, TEFC, frame 365TS, 3-phase, 60 Hz. Stoddard Silencer model PD33-C, part number 77A190, S.O. number 81183.



Makers Since 1950
 e: www.northstarice.com

MODEL **2093-B**
 PART NO. **77A190**
 S.O. NO. **01193**

Stoddard Silencers
 Grayslake, Illinois

LEESON

CC	100A	CE	
CAT. NO.	B-50045.60	FRAME	50313
MODEL	NR6134EP50	ENCL	IEFC
DUTY	CONT	MAX.AMB	40 °C
H.P.	75	VOLT	208-230/450
CODE	G	AMPS	160-172/85
S.F.	1.15	R.P.M.	3500
WGL	50.0	P.F.	91.2
LOAD TYPE	FLA FOR 75% V. DESI.	WGL	50.0

60 HZ

H.P.	60	VOLT	100/200
CODE	G	AMPS	144/81
S.F.	1.15	R.P.M.	3500
WGL	50.0	P.F.	91.2

LOW VOLTAGE: L1-T1-T2-T3-T4
 L2-T5-T6-T7-T8
 L3-T9-T10-T11-T12

HIGH VOLTAGE: L1-T1-T2-T3-T4
 L2-T5-T6-T7-T8
 L3-T9-T10-T11-T12

PRODUCT OF CHINA

LEESON ELECTRIC CORPORATION
 GRAFTON, WISCONSIN 53024 U.S.A. LEESON.COM

LR-02104