

Stainless Steel Cap Feeder

Mfg:

Model:

Stock No. FHF292a.1

Serial No.:

Stainless Steel Cap Feeder. Cap size: 5 in. dia. x 1 in. H. Bowl diameter: 23 in. Bronco II Variable Frequency Inverter, power supply input: 115/230 VAC, 15 amps, 50/60 Hz, power supply output: 0-90/0-180 VDC, 10 amps, 50/100 VDC-100/200 VDC, 1 amp. KB Penta Power DC Motor Speed Controller. Infeed height: 7 ft. 6 in. H. Exit height: 6 ft. 7 in. H. Overall dimensions: 3 ft. 4 in. L x 2 ft. 10 in. W x 7 ft. 6 in. H.



