

Chester Jensen Single Shell Tank- 200 Gallon

Mfg: Chester Jensen

Model: 70N20

Stock No. GAKD309.57a

Serial No. 7205

Chester Jensen Single Shell Tank- 200 Gallon. Model: 70N20. S/N: 7205. Maximum capacity: 367 gal. Tank dimensions: 74 in. dia. x 16 in. H (straight side). Dual motion agitation. Flip-top lids. Baldor Industrial Motor: 2 hp, 1160 rpm, 208-230/460 V, 6.5-6.2/3.1 amps, 60 Hz, 3 phase. Leeson Motor, 2 hp, 1165 rpm, 208-230/460 V, 7.2/3.6 FLA, 60 Hz, 3 phase. (2) Wormgear Reducers. Cone bottom and sidewalls are sheathed in bright stainless steel for operator protection, efficiency and appearance. Scraped surface agitation together with the high ratio of surface to product volume, provided by the 30° cone bottom design, maximizes thermal transfer rates in both heating and cooling modes. Inlets: (1) 1-1/4 in. dia. port, (1) 1-1/2 in. dia. threaded fitting (product). Outlets: (1) 3 in. dia. port. Overall dimensions: 76 in. L x 73 in. W x 88 in. H.





