

Wilden Stainless Steel Diaphragm Pump

Mfg: Wilden

Model: 316-SS

Stock No. GAWD009.6a

Serial No. 04-5000-03

Wilden Stainless Steel Diaphragm Pump. Model 316-SS. S/N: 04-5000-03. Flow rate: 81 GPM. Maximum pressure: 8.6 bar (125 psi). Suction lift: 18 ft. (dry). Inlets/outlets: (2) 1-1/2 in. pipes. Overall dimensions: 20 in. L x 16 in. W x 58 in. H. Max. suction lift capability 25 ft. (7.6 m). Max imum diameter (solids): 3/16 in. (4.8mm). Center section: aluminum, PFA coated, nikel plated, polypropylene. Air chambers: aluminum, PFA coated, nikel plated, mild steel, polypropylene.

