

## 1997 Unused Sussman Electric Boiler- 44 HP

Mfg: Sussman

Model: SVS-420

Stock No. GGEP001.20

Serial No. VS7-1006-U97

1997 Unused Sussman Electric Boiler- 44 HP. Model: SVS-420. S/N: VS7-1006-U97. Nat'l Bd: 190. For low or high pressure steam. Maximum designed steaming capacity: 1512 lb/hr. MAWP: 150 psig. Power requirements: 480 V, 520 amps, 60 Hz, 3 phase. Control requirements: 120 V, 1.7 amps. Standard features on the Sussman boiler include: 2 in. thick insulation, vertically mounted incoloy sheathed immersion elements complete with epoxy and seal, liquid level gauge glass assembly, main and auxiliary low water cutt off controls, manual reset high limit pressure controls, and industrial rated magnetic contactors. Inlets: (1) 3/4 in. dia. feed pipe. Outlets: (1) 1-1/2 in. dia. blowoff, (1) 1-1/2 in. dia. safety valve, (1) 3 in. dia. pipe. Overall dimensions: 44 in. L x 43 in. W x 64 in. H.

Applications include steam for: chemical tanks, reactors, dystillations and autoclaves, dyestuffs, food processing, jacketed vessels for processing, pipe tracing, viscous material, fuel-oil line heating, antifreeze protection, comfort heating and humidification. Honeywell Pressuretrol Controllers.



